

KADO CLEAN PROFESSIONAL UO-S2 4" REVERSE OSMOSIS SYSTEM

APPLICATIONS

Steam boilers, heating and cooling circuits, breweries and beverage production, livestock and poultry farms, glazing factories, laundry and car wash etc.

EQUIPMENT

- Grundfos® CM 1-10 pump
- 300 psi membrane vessels
- BB10 sediment prefilter
- Electrical panel with Eco UO 1 Controller
- Danfoss solenoid valves
- Piping, instrumentation
- Steel frame
- Wooden crate

KEY FEATURES

- Eco UO 1 Controller
- Easy to use thanks to smart architecture
- Universal system construction allows connecting options of permeate flushing and raw water blending
- Grundfos worldwide guaranty
- CE marked and confirmed to be safe in accordance with EC New Approach Directives

OPTIONS

- Filmtec™ XLE-4040 / LCLE-4040 or ELP-4040 membrane Dosing pump for antiscalant
- Versatile set for raw water blending (30...240 L/h) or permeate flushing

PHYSICAL PARAMETERS

Influent water, concentrate, permeate	G ½"	
Antiscalant dosing port	G ½"	
Permeate flushing input port	G ½"	
Approx. weight (bare system / crate)	60 kg	85 kg
Dimensions (bare system, W × D × H)	0.55 × 0.42 × 1.50 m	
Dimensions (crate, W × D × H)	0.60 × 0.50 × 1.65 m	



Ecosoft reserves the right to amend the product's system architecture provided that its functionality and usability will not deteriorate

KADO CLEAN PROFESSIONAL UO S2 4" REVERSE OSMOSIS SYSTEM

Code	Product	Flow rate, L/h (GPH)	Membranes
UO12000TPS	KADO CLEAN PROFESSIONAL UO S2	400–550 (100–150)	2/40 × 40


TECHNICAL SPECIFICATION

Permeate capacity ¹	500 L/h
Permeate recovery ²	75%
Maximum TDS	3000 mg/L
Influent flow demand	650...800 L/h (service) 1500...2000 L/h (rinse)
Operating pressure	8...12 bar
Maximum pressure	14 bar
Electrical requirements	230 V, 50 Hz (1 ph)
Electrical power	0.7 kW
Prefilter rating	5 µm

¹ depends on feed water TDS, temperature, and permeate recovery — see graph on the right

² for low scaling/fouling water

KADO CLEAN UO S2 FLOW CAPACITY (WITH XLE-4040 MEMBRANES)



Permeate flow rates are calculated under the following conditions:
 • 2 bar influent water pressure
 • 0 bar backpressure in the permeate line
 • fresh membranes
 • XLE-4040 membranes

PIPES AND INSTRUMENTS DIAGRAM

